

Product data sheet

Specifications



APC Smart-UPS X, Line
Interactive, 2200VA, Rack/tower
convertible 2U, 208V-230V, 8x
C13+1x C19 IEC, SmartSlot,
Extended runtime

SMX2200RMHV2U

Overview

Presentation	Intelligent and efficient network power protection from entry level to scalable runtime. Ideal UPS for servers, point-of-sale, routers, switches, hubs and other network devices.
Lead Time	Usually in Stock

Main

Main Input Voltage	208 V 230 V
Other Input Voltage	220 V 240 V
Main Output Voltage	208 V 230 V
Other Output Voltage	220 V 240 V
Rated Power In W	1980 W
Rated Power In Va	2200 VA
Input Connection Type	IEC 320 C20 Schuko CEE 7 / EU1-16P BS1363A British
Output Connection Type	8 IEC 320 C13 2 IEC Jumpers 1 IEC 320 C19
Number Of Rack Unit	2U
Cable Length	1.83 m
Number Of Cables	1
Battery Type	Lead-acid battery
Provided Equipment	CD with software Documentation CD Smart UPS signalling RS-232 cable User manual USB cable Rack mounting brackets

Batteries & Runtime

Run Time	View Runtime Graph
Efficiency	View Efficiency Graph
Extended Runtime	1
Number Of Battery Filled Slots	0

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Battery Free Slots	0
Battery Recharge Time	3 h
Number Of Battery Replacement Quantity	1
Battery Life	3...5 year(s)
Replacement Battery	APCRBC117 
Battery Charger Power	233 W rated

General

Number Of Power Module	1750
Number Of Power Module Filled Slots	0
Number Of Power Module Free Slots	0
Product Web Sub-Family	Extended run
Redundant	No

Physical

Colour	Black
Height	8.5 cm
Width	43.2 cm
Depth	66.7 cm
Net Weight	37.32 kg
Mounting Location	Front
Mounting Preference	Lower
Mounting Mode	Rack-mounted
Two Post Mountable	0
Usb Compatible	Yes

Input

Input Voltage Limits	140...280 V
Network Frequency	50/60 Hz +/- 3 Hz auto-sensing

Output

Harmonic Distortion	Less than 5 %
Maximum Configurable Power In Va	2200 VA
Maximum Configurable Power In W	1980 W
Transfer Time	2-4 ms 6 ms typical : 10 ms maximum
Ups Type	Line interactive
Wave Type	Sine wave
Output Frequency	50/60 Hz +/- 3 Hz sync to mains

Conformance

Product Certifications	CE CSA EAC IRAM RCM VDE
Standards	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018

Environmental

Acoustic Level	55 dBA
Heat Dissipation	150 Btu/h
Operating Altitude	0...10000 ft
Ambient Air Temperature For Operation	0...40 °C
Ambient Air Temperature For Storage	-15...45 °C
Storage Altitude	0.00...15240.00 m
Relative Humidity	0...95 %
Storage Relative Humidity	0...95 %

Communications & Management

Control Panel	LED status display with load and battery bar-graphs and on line : on battery : replace battery : and overload indicators Multifunction LCD status and control console
Emergency Power Off	Yes
Free Slots	1
Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays

Surge Protection and Filtering

Surge Energy Rate	645 J
Noise Suppression	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : meets UL 1449

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	24.3 cm
Package 1 Width	59.6 cm
Package 1 Length	86.9 cm
Package 1 Weight	45.36 kg
Unit Type Of Package 2	PAL
Number Of Units In Package 2	8
Package 2 Height	111 cm
Package 2 Width	100 cm
Package 2 Length	120 cm
Package 2 Weight	384 kg

Pallet Unit Layers	2
Pallet Layers	4

Contractual warranty

Warranty	3 years repair or replace (excluding battery) and 2 years for battery, optional on-site warranties available, optional extended warranties available
----------	--

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

[Learn more about Green Premium >](#)



Energy Efficient Take-back Transparency RoHS/REACH

Resource performance

 Energy Efficient Product

 Take-Back Program Available

Well-being performance

 Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information