

Product datasheet

Specifications



APC Smart-UPS, Line Interactive, 1000VA, Tower, 230V, 8x IEC C13 outlets, SmartSlot, AVR, LCD

SMT1000I

Overview

Presentation Intelligent and efficient network power protection from entry level to scalable runtime. Ideal UPS for servers, point-of-sale, routers, switches, hubs and other network devices.

Lead time Usually Ships within 2 Weeks

Main

Main Input Voltage 230 V

Other Input Voltage 220 V
240 V

Main Output Voltage 230 V

Other Output Voltage 220 V
240 V

Rated power in W 700 W

Rated power in VA 1000 VA

Input Connection Type IEC 320 C14

Nb of power socket outlets 8 IEC 320 C13
2 IEC Jumpers

Battery type Lead-acid battery

Provided equipment USB cable
Documentation CD
Installation guide
Smart UPS signalling RS-232 cable

General

Number of power module filled slots 0

Number of power module free slots 0

Redundant No

Physical

Colour Black

Height 21.9 cm

Width 17.1 cm

Depth 43.9 cm

Net weight 18.86 kg

Mounting location	Front
Mounting preference	No preference
Mounting mode	Not rack-mountable
Two post mountable	0
USB compatible	No

Input

Input voltage limits	151...302 V adjustable 160...286 V
Network frequency	50/60 Hz +/- 3 Hz auto-sensing

Output

Harmonic distortion	Less than 5 % at full load
Maximum configurable power in VA	1000 VA
Maximum configurable power in W	700 W
UPS type	Line interactive
Wave type	Sine wave
Output frequency	47...53 Hz for 50 Hz nominal sync to mains 57...63 Hz for 60 Hz nominal sync to mains

Conformance

Product certifications	CE EAC RCM VDE
------------------------	-------------------------

Environmental

Acoustic level	41 dBA
Heat dissipation	100 Btu/h
Operating altitude	0...10000 ft
Ambient air temperature for operation	0...40 °C
Ambient air temperature for storage	-15...45 °C
Storage altitude	0.00...15240.00 m
Relative humidity	0...95 %
Storage Relative Humidity	0...95 %

Batteries & Runtime

Additional information	Configurable for 220 : 230 or 240 nominal output voltage
Extended runtime	0
Number of battery filled slots	0
Number of battery free slots	0
Battery recharge time	3 h
Number of battery replacement quantity	1
Battery life	3...5 year(s)

Battery power in VAH	264 VAh runtime
Battery charger power	88 W rated

Communications & Management

Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm
Control panel	Multifunction LCD status and control console
Emergency power off	Optional
Free slots	1

Surge Protection and Filtering

Surge energy rate	459 J
Noise suppression	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : meets UL 1449

Packing Units

Package 1 Weight	22.77 kg
Package 1 Height	37.6 cm
Package 1 width	32.8 cm
Package 1 Length	59.5 cm
SCC14	731304268673
Number of Units in Package 3	12

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	3 years repair or replace (excluding battery) and 2 years for battery
----------	---