

Product datasheet

Specifications



APC Smart-UPS, Line Interactive, 2200VA, Tower, 230V, 8x IEC C13+2x IEC C19 outlets, SmartConnect Port+SmartSlot, AVR, LCD

SMT2200IC

Overview

Presentation	Intelligent and efficient network power protection from entry level to scalable runtime. Ideal UPS for servers, point-of-sale, routers, switches, hubs and other network devices.
Lead time	Usually in Stock

Main

Main Input Voltage	230 V
Other Input Voltage	220 V 240 V
Main Output Voltage	230 V
Other Output Voltage	220 V 240 V
Rated power in W	1980 W
Rated power in VA	2200 VA
Input Connection Type	IEC 320 C20 Schuko CEE 7 / EU1-16P BS1363A British
Nb of power socket outlets	8 IEC 320 C13 2 IEC Jumpers 1 IEC 320 C19
Number of rack unit	0U
Number of cables	1
Battery type	Lead-acid battery
Provided equipment	USB cable

General

Number of power module filled slots	0
Number of power module free slots	0
Product web sub-family	Cloud-enabled monitoring
Redundant	No

Physical

Colour	Black
--------	-------

Height	43.5 cm
Width	19.7 cm
Depth	54.4 cm
Net weight	50.2 kg
Mounting location	Front
Mounting preference	No preference
Mounting mode	Not rack-mountable
Two post mountable	0
USB compatible	Yes

Input

Input voltage limits	151...302 V adjustable 160...286 V
Network frequency	50/60 Hz +/- 3 Hz auto-sensing

Output

Harmonic distortion	Less than 5 %
Maximum configurable power in VA	2200 VA
Maximum configurable power in W	1980 W
Transfer time	6 ms typical : 10 ms maximum
UPS type	Line interactive
Wave type	Sine wave
Output frequency	50/60 Hz +/- 3 Hz sync to mains

Conformance

Product certifications	CE EAC RCM VDE
Standards	EN/IEC 62040-1 EN/IEC 62040-2

Environmental

Acoustic level	45 dBA
Heat dissipation	275 Btu/h
Operating altitude	0...10000 ft
Ambient air temperature for operation	0...40 °C
Ambient air temperature for storage	-15...45 °C
Storage altitude	0.00...15240.00 m
Relative humidity	0...95 %
Storage Relative Humidity	0...95 %

Batteries & Runtime

Additional information	Configurable for 220 : 230 or 240 nominal output voltage
Extended runtime	0

Number of battery filled slots	0
Number of battery free slots	0
Battery recharge time	3 h
Number of battery replacement quantity	1
Battery life	3...5 year(s)
Battery power in VAH	783 VAh runtime
Battery charger power	260 W rated

Communications & Management

Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays
Control panel	Multifunction LCD status and control console
Emergency power off	Yes
Free slots	1

Surge Protection and Filtering

Surge energy rate	365 J
Noise suppression	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : meets UL 1449

Packing Units

Package 1 Weight	61.9 kg
Package 1 Height	69.9 cm
Package 1 width	38.1 cm
Package 1 Length	76.2 cm
Number of Units in Package 3	9

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	3 years repair or replace (excluding battery) and 2 years for battery, optional on-site warranties available, optional extended warranties available
----------	--