

# Product datasheet

Specifications



## Rack ATS, 200/208V, 20A, L6-20 in, (8) C13 (1) C19 out



AP4430

⚠ To be discontinued on: 30 December 2022

⚠ To be discontinued

### Overview

Lead time Usually in Stock

### Main

|                       |   |
|-----------------------|---|
| Main Input Voltage    | 200 V<br>208 V  |
| Main Output Voltage   | 200 V<br>208 V  |
| Input Connection Type | NEMA L6-20P   |
| Number of rack unit   | 1U  |
| Cable length          | 2.44 m  |
| Number of cables      | 2   |
| Provided equipment    | Mounting hardware<br>Rack mounting brackets<br>RS-232 configuration cable |

### Physical

|                     |               |
|---------------------|---------------|
| Height              | 4.4 cm        |
| Width               | 43.2 cm       |
| Depth               | 23.6 cm       |
| Net weight          | 4.83 kg       |
| Mounting location   | Front<br>Rear |
| Mounting preference | No preference |
| Mounting mode       | Rack-mounted  |

### Input

|                      |          |
|----------------------|----------|
| Network frequency    | 50/60 Hz |
| [In] rated current   | 16 A     |
| Max line current     | 20 A     |
| Input current limits | 20 A     |
| Load capacity        | 3300 VA  |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Output

|                                |                                    |
|--------------------------------|------------------------------------|
| Max current draw               | 20 A                               |
| Number of power socket outlets | 8 IEC 60320 C13<br>1 IEC 60320 C19 |
| Protection type                | Without circuit breaker            |

## Conformance

|           |   |
|-----------|---|
| Standards | EN 55022 class A<br>FCC part 15 class A |
|-----------|---|

## Environmental

|                                       |                   |
|---------------------------------------|-------------------|
| Ambient air temperature for operation | -5...45 °C        |
| Relative humidity                     | 5...95 %          |
| Operating altitude                    | 0...10000 ft      |
| Ambient air temperature for storage   | -25...65 °C       |
| Storage Relative Humidity             | 5...95 %          |
| Storage altitude                      | 0.00...15240.00 m |

## Packing Units

|                  |         |
|------------------|---------|
| Package 1 Weight | 6.6 kg  |
| Package 1 Height | 11.4 cm |
| Package 1 width  | 60 cm   |
| Package 1 Length | 35.6 cm |

## Offer Sustainability

|                            |  |
|----------------------------|--|
| Sustainable offer status   | Green Premium product                            |
| REACH Regulation           | <a href="#">REACH Declaration</a>                |
| EU RoHS Directive          | Compliant<br><a href="#">EU RoHS Declaration</a> |
| Lead free                  | Yes  |
| Mercury free               | Yes  |
| RoHS exemption information | <a href="#">Yes</a>                              |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>    |
| Circularity Profile        | <a href="#">End of Life Information</a>          |
| Take-back                  | Take-back program available                      |

## Contractual warranty

|          |                           |
|----------|---------------------------|
| Warranty | 2 years repair or replace |
|----------|---------------------------|