

Product datasheet

Specifications



Smart-UPS X 750VA rackmount / tower LCD 230V

SMX750I

Overview

Presentation	Intelligent and efficient network power protection from entry level to scalable runtime. Ideal UPS for servers, point-of-sale, routers, switches, hubs and other network devices.
Lead time	Usually Ships within 2 Weeks

Main

Main Input Voltage	230 V
Other Input Voltage	220 V 240 V
Main Output Voltage	230 V
Rated power in W	600 W
Rated power in VA	750 VA
Plug standard	IEC 320 C14
Nb of power socket outlets	8 IEC 320 C13 2 IEC Jumpers
Number of rack unit	2U
Cable length	1.83 m
Number of cables	1
Battery type	Lead-acid battery
Provided equipment	CD with software Documentation CD Installation guide Rack mounting brackets Removable support feet Smart UPS signalling RS-232 cable User manual

General

Number of power module filled slots	0
Number of power module free slots	0
Product web sub-family	Extended run
Redundant	No

Physical

Colour	Black
---------------	-------

Height	8.9 cm
Width	43.2 cm
Depth	49 cm
Net weight	22.05 kg
Mounting preference	Lower
Mounting mode	Rack-mounted with kit
Two post mountable	1
USB compatible	No

Input

Input voltage limits	151...302 V adjustable 160...286 V
Network frequency	50/60 Hz +/- 3 Hz auto-sensing

Output

Harmonic distortion	Less than 5 %
Maximum configurable power in VA	750 VA
Maximum configurable power in W	600 W
UPS type	Line interactive
Wave type	Sine wave
Output frequency	50/60 Hz +/- 3 Hz sync to mains

Conformance

Product certifications	CE RCM VDE EAC
Standards	EN/IEC 62040-1 EN/IEC 62040-2

Environmental

Acoustic level	40 dBA
Heat dissipation	69 Btu/h
Operating altitude	0...10000 ft
Ambient air temperature for operation	0...40 °C
Ambient air temperature for storage	-15...45 °C
Storage altitude	0.00...15240.00 m
Relative humidity	0...95 %
Storage Relative Humidity	0...95 %

Batteries & Runtime

Extended runtime	0
Number of battery filled slots	1
Number of battery free slots	1
Battery recharge time	3 h

Number of battery replacement quantity	1
Overcurrent protection	60 A
Battery life	3...5 year(s)
Battery power in VAH	312 VAh runtime
Battery charger power	104 W rated
Battery option	SMX48RMBP2U 1 938 VAh SMX48RMBP2U 2 1563 VAh SMX48RMBP2U 3 2188 VAh SMX48RMBP2U 4 2613 VAh SMX48RMBP2U 5 3438 VAh

Communications & Management

Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm
Control panel	Multifunction LCD status and control console
Free slots	1

Surge Protection and Filtering

Surge energy rate	645 J
Noise suppression	Full time multi-pole noise filtering : 5% IEEE surge let-through : zero clamping response time : meets UL 1449

Packing Units

Package 1 Weight	26.444 kg
Package 1 Height	24.638 cm
Package 1 width	58.928 cm
Package 1 Length	61.976 cm
Number of Units in Package 3	8

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	3 years repair or replace (excluding battery) and 2 years for battery
----------	---