Product datasheet

Specification





Easy UPS 3S 10kVA 400V 3:3 UPS for internal batteries

E3SUPS10KHB

Overview

Presentation	High-efficiency 3-phase UPS that features advanced product features, competitive specifications, and robust electrical design, making business continuity easy in the data center or electrical room. This is an exceptionally easy to install, operate, maintain, and service 10 kVA UPS, ideal for small and medium businesses. Includes dust filter and conformance-coated boards for harsh environments. This UPS is for internal batteries, but is supplied without batteries, so you can easily customize the battery runtime. For battery runtime details, see the runtime charts published under the Documents tab.
Land Time	

Lead Time Usually Ships within 6 Weeks

Main

Mairi		
Main Input Voltage	400 V 3 phases	
Other Input Voltage	380 V 415 V	
Main Output Voltage	400 V 3 phases	
Other Output Voltage	380 V 415 V	
Rated Power In W	10 kW	
Rated Power In Va	10 kVA	
Provided Equipment	Dust filter	

Batteries & Runtime

Efficiency	View Efficiency Graph ☐
Battery Type	VRLA
Battery Voltage	240 V
Maximum Short-Circuit Current	10 kA
Number Of Battery Filled Slots	0
Number Of Battery Free Slots	3
Discharge Battery Voltage	+/- 198 V DC

Physical

Colour	White (RAL 9003)
Height	140 cm
Width	38 cm
Depth	92.8 cm
Net Weight	112 kg



Usb Compatible	Yes	

Input

Maximum Input Current	18 A
Input Harmonic Distortion	Less than 3 % for full load
Load Power Factor	0.9 leading to 0.9 lagging
Input Power Factor At Full Load	0.99
Input Voltage Limits	304477 V
Network Frequency	4565 Hz

Output

<u> </u>	
Maximum Configurable Power In Va	10 kVA
Maximum Configurable Power In W	10 kW
Output Frequency	50 Hz sync to mains 60 Hz sync to mains
Harmonic Distortion	Less than 3 %
Output Harmonic Distortion	< 3% linear load
Output Overload Operation	130-150% for 1 minute and 125-130% for 10 minutes
Output Voltage Tolerance	+/- 1.5 %
Ups Type	Double conversion online

Conformance

Product Certifications	CE	
	EAC	
	RCM	

Environmental

Ambient Air Temperature For Operation	040 °C
Relative Humidity	095 % non-condensing
Operating Altitude	03333 ft
Ambient Air Temperature For Storage	-1540 °C
Storage Relative Humidity	095 % non-condensing
Storage Altitude	0.0015240.00 m
Acoustic Level	60 dBA
Heat Dissipation	516 W
Ip Degree Of Protection	IP20

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	164 cm
Package 1 Width	101.4 cm
Package 1 Length	56.3 cm

Package 1 Weight

145 kg

Contractual warranty

Warranty

1 year on-site repair or replace with factory authorized Start-Up



Sustainability Green Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO2 products.

Learn more about Green Premium >





Transparency RoHS/REACh

Well-being performance



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information