Specifications





# APC NetShelter Metered Rack PDU, 2U, 1PH, 7.4kW 230V 32A, x12 C13 and x4 C19 outlets, IEC 309 cord

AP7822B

#### Overview

Lead Time

Lead Time	Usually in Stock	
Main		
Pdu Type	Metered	
Cord Length	3.66 m	
Number Of Cables	1	
Provided Equipment	Cord retention bracket(s) Installation guide Rack mounting brackets User manual	

## Complementary

<u> </u>	
Input Voltage	200 V
	208 V
	230 V
	200 V
Height	8.8 cm
Width	44.4 cm
Output Voltage	230 V
Depth	11.2 cm
Net Weight	3.36 kg
Mounting Location	Front
	Rear
Mounting Preference	No preference
Input Plug Type	IEC 60309 32 A 2P + E
Mounting Mode	Rack-mounted
Rack Units	2U
Manuation Desition	
Mounting Position	Horizontal
Input Current Limits	32 A
Load Capacity	7400 VA
Network Frequency	50/60 Hz
Outlet Type And Quantity	12 IEC 60320 C13 4 IEC 60320 C19

## Environment



Product Certifications	C-Tick CE GOST IRAM MIC VDE VCCI
Standards	FCC part 15 class A ICES-003
Ambient Air Temperature For Operation	-545 °C
Relative Humidity	595 %
Operating Altitude	010000 ft
Ambient Air Temperature For Storage	-2565 °C
Storage Relative Humidity	595 %
Storage Altitude	0.0015240.00 m

# **Packing Units**

_	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	14 cm
Package 1 Width	36.8 cm
Package 1 Length	50.8 cm
Package 1 Weight	5.42 kg

#### **Contractual warranty**

Warranty

2 years repair or replace

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.



#### **Resource performance**

Zenergy Efficient Product

Take-Back Program Available

#### Well-being performance

Mercury Free

Rohs Exemption Information Yes

## **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information



