Product datasheet





APC Smart-UPS On-Line, 5kVA, Tower, 230V, 6x C13+4x C19 IEC outlets, Network Card+SmartSlot, Extended runtime, W/O rail kit

SRT5KXLI

Overview

Presentation	High density, double-conversion on-line power protection with scalable runtime.
Lead Time	Usually in Stock
Main	
Main Input Voltage	230 V
Other Input Voltage	220 V 240 V
Main Output Voltage	230 V
Other Output Voltage	220 V 240 V
Rated Power In W	4500 W
Rated Power In Va	5000 VA
Output Connection Type	6 IEC 60320 C13 2 IEC Jumpers 4 IEC 60320 C19
Provided Equipment	CD with software Communication cable Documentation CD Installation guide Removable support feet Temperature probe USB cable Warranty card Web/SNMP management card

Batteries & Runtime

Run Time	View Runtime Graph ☐
Efficiency	View Efficiency Graph ☐
Battery Type	Lead-acid battery
Number Of Battery Filled Slots	2
Number Of Battery Free Slots	0
Battery Recharge Time	1.5 h
Number Of Battery Replacement Quantity	1
Battery Voltage	192 V
Battery Charger Power	560 W rated
Battery Life	35 year(s)
Replacement Battery	APCRBC140 ☐



Extended Runtime

General

Ups Type	Double conversion online
Product Web Sub-Family	High density
Number Of Power Module Free Slots	0
Number Of Power Module Filled Slots	0
Redundant	No

Physical

•	
Colour	Black
Height	43.2 cm
Width	13 cm
Depth	71.94 cm
Net Weight	54.43 kg
Mounting Location	Front
Mounting Preference	No preference
Mounting Mode	Rack-mounted with kit
Two Post Mountable	0
Usb Compatible	Yes

Input

Network Frequency	4070 Hz auto-sensing
Number Of Input Connectors	1 hard wire 3-wire (1P + N + E)
Input Voltage Limits	100275 V adjustable (half load)

Output

Maximum Configurable Power In Va	5000 VA
Maximum Configurable Power In W	4500 W
Output Frequency	50/60 Hz +/- 3 Hz sync to mains
Wave Type	Sine wave
Harmonic Distortion	Less than 2 %
Crest Factor	3:1
Bypass Type	Internal bypass (automatic and manual)

Conformance

Product Certifications	CE		
	EAC		
	IRAM RCM		
	VDE		
Marking	CE Mark		
Standards	EN/IEC 62040-1:2019/A11:2021		
	EN/IEC 62040-2:2006/AC:2006		
	EN/IEC 62040 2:2049		

Environmental

Ambient Air Temperature For Operation	040 °C
Relative Humidity	095 % non-condensing
Operating Altitude	010000 ft
Ambient Air Temperature For Storage	-1545 °C
Storage Relative Humidity	095 % non-condensing
Storage Altitude	0.0015240.00 m
Acoustic Level	55 dBA
Heat Dissipation	931 Btu/h
Ip Degree Of Protection	IP20

Communications & Management

Free Slots	1	
Preinstalled Device	Network management card 3 with environmental monitoring	
Alarm	Audible and visible alarms : prioritized by severity	
Emergency Power Off	Yes	

Surge Protection and Filtering

Surge Energy Rate 480 J

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	33 cm
Package 1 Width	61 cm
Package 1 Length	96 cm
Package 1 Weight	63.6 kg

Contractual warranty

Warranty 3 years repair or replace (excluding battery) and 2 years for battery



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Learn more about Green Premium >










Energy Efficient Take-back Transparency RoHS/REACh

Resource performance





Take-Back Program Available

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information