



APC Smart-UPS X, Line Interactive, 3kVA, Rack/tower convertible 4U, 208V-230V, 8x C13+2x C19 IEC, SmartSlot, Extended runtime, Short depth

SMX3000HV

Overview

Intelligent and efficient network power protection from entry level to scalable runtime. Ideal UPS for servers, point-of-sale, routers, switches, hubs and other network devices.
Usually in Stock
208 V
230 V
220 V
240 V
230 V
208 V
220 V
240 V
2700 W
3000 VA
IEC 320 C20
Schuko CEE 7 / EU1-16P
BS1363A British
8 IEC 320 C13
2 IEC Jumpers
2 IEC 320 C19
4U
1.83 m
1
Lead-acid battery
CD with software Documentation CD Smart UPS signalling RS-232 cable User manual USB cable Rack mounting brackets

Batteries & Runtime

Run Time	View Runtime Graph ☐
Efficiency	View Efficiency Graph ☐
Extended Runtime	1
Number Of Battery Filled Slots	0

Number Of Battery Free Slots	0
Battery Recharge Time	3 h
Number Of Battery Replacement Quantity	1
Battery Life	35 year(s)
Replacement Battery	APCRBC143 ☐
Battery Charger Power	245 W rated

General

Number Of Power Module	2400
Number Of Power Module Filled Slots	0
Number Of Power Module Free Slots	0
Product Web Sub-Family	Extended run
Redundant	No

Physical

Colour	Black
Height	43.2 cm
Width	17.8 cm
Depth	48.3 cm
Net Weight	38.64 kg
Mounting Location	Front
Mounting Preference	Lower
Mounting Mode	Rack-mounted
Two Post Mountable	1
Usb Compatible	Yes

Input

Input Voltage Limits	140280 V
Network Frequency	50/60 Hz +/- 3 Hz auto-sensing

Output

Crest Factor	3:1
Harmonic Distortion	Less than 5 %
Maximum Configurable Power In Va	3000 VA
Maximum Configurable Power In W	2700 W
Transfer Time	6 ms typical : 10 ms maximum
Ups Type	Line interactive
Wave Type	Sine wave
Output Frequency	50/60 Hz +/- 3 Hz sync to mains

Conformance

Product Certifications	CE EAC IRAM RCM TISI VDE
Standards	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018

Environmental

Acoustic Level	55 dBA
Heat Dissipation	184 Btu/h
Operating Altitude	010000 ft
Ambient Air Temperature For Operation	040 °C
Ambient Air Temperature For Storage	-1545 °C
Storage Altitude	0.0015240.00 m
Relative Humidity	095 %
Storage Relative Humidity	095 %

Communications & Management

Control Panel	Multifunction LCD status and control console
Emergency Power Off	Yes
Free Slots	1
Control Panel	LED status display with on line : on battery : replace battery and overload indicators
Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays

Surge Protection and Filtering

Surge Energy Rate	645 J
Noise Suppression	Full time multi-pole noise filtering: 0.3% IEEE surge let-through: zero clamping response time: meets UL 1449

Packing Units

_	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	33 cm
Package 1 Width	63.3 cm
Package 1 Length	58.6 cm
Package 1 Weight	47.73 kg
Pallet Unit Layers	2
Pallet Layers	4

Logistical informations

Country Of Origin PH

Contractual warranty

Warranty

3 years repair or replace (excluding battery) and 2 years for battery, optional on-site warranties available, optional extended warranties available



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO2 products.

Learn more about Green Premium >









Energy Efficient Take-back Transparency RoHS/REACh

Resource performance

Energy Efficient Product



Take-Back Program Available

Well-being performance



Rohs Exemption Information

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information