Product data sheet



Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Mounting Mode

Mounting Position

Line Rated Current

Rack Units



Rack-mounted

0U

Vertical

16 A

Acceptable Input Voltage	100240 V
Input Current Limits	20 A
Load Capacity	3300 VA
Input Frequency	50/60 Hz
Total Number Of Outlets	21 IEC 60320 C13 3 IEC 60320 C19

Environment

Product Certifications	UL Listed VCCI Class A VDE
Standards	EN 55022 Class A EN 55024 EN 61000-3-2 EN 61000-3-3 FCC Part 15 class A ICES-003
Ambient Air Temperature For Operation	23140 °F (-560 °C)
Relative Humidity	595 %
Operating Altitude	010000 ft
Ambient Air Temperature For Storage	-13149 °F (-2565 °C)
Storage Relative Humidity	595 %
Storage Altitude	050000 ft (0.0015240.00 m)

Ordering and shipping details

Category	80230-IG SEBA TO SEUSA
Discount Schedule	BMS1
Gtin	731304317579
Returnability	No
Country Of Origin	IN

Packing Units

_	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	80.20 in (203.7 cm)
Package 1 Width	4.61 in (11.7 cm)
Package 1 Length	6.42 in (16.3 cm)
Package 1 Weight	19.91 lb(US) (9.03 kg)

Contractual warranty

Warranty

2 years repair or replace

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.



Resource performance

Zenergy Efficient Product

Take-Back Program Available

Well-being performance



Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information

