

# Product data sheet

Specifications



## APC Power-Saving Back-UPS XS 1500VA

BX1500G

! Discontinued on: 09 September 2021

! End-of-service on: 12 November 2022

! Discontinued

### Overview

Lead time Usually in Stock

### Main

Main Input Voltage	120 V
Kw Rating	865 W
Rated power in VA	1500 VA
Output connection type	5 NEMA 5-15R 5 NEMA 5-15R surge
Cable length	6 ft (1.83 m)
Number of cables	1
Battery Type	Lead-Acid battery

### General

Provided equipment	User Manual USB cable
Number of power module free slots	0
Number of power module filled slots	0
Redundant	No

### Physical

Color	Black
Height	11.85 in (30.1 cm)
Width	4.41 in (11.2 cm)
Depth	15.04 in (38.2 cm)
Net Weight	23.81 lb(US) (10.8 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable
Two post mountable	0
USB compatible	No

## Input

Input Frequency	50/60 Hz +/- 3 Hz auto-sensing
-----------------	--------------------------------

## Output

Max Configurable Power (Watts)	865 W
--------------------------------	-------

Output frequency	50/60 Hz +/- 3 Hz sync to mains
------------------	---------------------------------

Topology	Line Interactive
----------	------------------

Waveform Type	Stepped approximation to a sinewave
---------------	-------------------------------------

Maximum configurable power in VA	1500 VA
----------------------------------	---------

Transfer Time	8ms typical : 12ms maximum
---------------	----------------------------

## Conformance

Product Certifications	California (CEC) Battery Charger TÜV
------------------------	---

Equipment protection policy	Lifetime : \$150000
-----------------------------	---------------------

## Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
---------------------------------------	-------------------------

Relative Humidity	0...95 %
-------------------	----------

Operating altitude	0...30000 ft
--------------------	--------------

Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
-------------------------------------	--------------------------

Storage Relative Humidity	0...95 %
---------------------------	----------

Storage altitude	0...50000 ft (0.00...15240.00 m)
------------------	----------------------------------

## Batteries & Runtime

Included Battery Modules	1
--------------------------	---

Battery Slots Empty	0
---------------------	---

Typical recharge time	16 h
-----------------------	------

RBC Quantity	1
--------------	---

Battery Charge Power (Watts)	13 W rated
------------------------------	------------

Battery power in VAH	187 VAh capacity 216 VAh runtime
----------------------	-------------------------------------

Battery Life	3...5 year(s)
--------------	---------------

Replacement battery	<a href="#">APCRBC124</a> 
---------------------	---

	<a href="#">BR1500BPG</a> 
--	---

Extendable Run Time	0
---------------------	---

## Communications & Management

Control panel	Multi-function LCD status and control console
---------------	---

## Surge Protection and Filtering

Surge energy rating	354 J
---------------------	-------

Filtering	Full time multi-pole noise filtering : 5% IEEE surge let-through : zero clamping response time : mee
-----------	--

---

Let Through Voltage Rating	330 V
----------------------------	-------

## Ordering and shipping details

---

GTIN	731304268390
------	--------------

## Packing Units

---

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	15.24 in (38.7 cm)
Package 1 Width	19.21 in (48.8 cm)
Package 1 Length	9.37 in (23.8 cm)
Package 1 Weight	26.46 lb(US) (12 kg)
SCC14	10731304268397

## Offer Sustainability

---

Sustainable offer status	Green Premium product
--------------------------	-----------------------

---

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
---------------------------	---

---

REACH Regulation	<a href="#">REACH Declaration</a>
------------------	-----------------------------------

---

EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
-------------------	--

---

Mercury free	Yes
--------------	-----

---

RoHS exemption information	<a href="#">Yes</a>
----------------------------	---------------------

---

Environmental Disclosure	<a href="#">Product Environmental Profile</a>
--------------------------	---

---

Circularity Profile	<a href="#">End of Life Information</a>
---------------------	---

---

Optimized Energy Efficiency	Energy efficient product
-----------------------------	--------------------------

---

Take-back	Take-back program available
-----------	-----------------------------

---

## Contractual warranty

---

Warranty	3 years repair or replace
----------	---------------------------

## Recommended replacement(s)