



APC Smart-UPS, Line Interactive, 2200VA, Rackmount 2U, 230V, 8x IEC C13+2x IEC C19 outlets, Network Card, AVR, LCD

SMT2200RMI2UNC

#### **Overview**

Presentation	Intelligent and efficient network power protection from entry level to scalable runtime. Ideal UPS for servers, point-of-sale, routers, switches, hubs and other network devices.				
Lead Time	Usually in Stock				
Main					
Main Input Voltage	230 V				
Other Input Voltage	220 V 240 V				
Main Output Voltage	230 V				
Other Output Voltage 220 V 240 V					
Rated Power In W	1980 W				
Rated Power In Va	2200 VA				
Input Connection Type	BS1363A British IEC 320 C20 Schuko CEE 7 / EU1-16P				
Output Connection Type	8 IEC 320 C13 3 IEC Jumpers 1 IEC 320 C19				
Number Of Rack Unit	2U				
Cable Length	2.00 m				
Number Of Cables	1				
Battery Type	Lead-acid battery				
Provided Equipment	CD with software Documentation CD Installation guide Rack mounting hardware Rack mounting support rails Smart UPS signalling RS-232 cable Temperature probe USB cable				

### **Batteries & Runtime**

Run Time	View Runtime Graph ☐				
Efficiency	View Efficiency Graph ☐				
Additional Information	Configurable for 220 : 230 or 240 nominal output voltage				
Extended Runtime	0				
Number Of Battery Filled Slots	0				

Number Of Battery Free Slots	0
Battery Recharge Time	3 h
Number Of Battery Replacement Quantity	1
Battery Life	35 year(s)
Replacement Battery	RBC43 □
Battery Charger Power	169 W rated

## General

Number Of Power Module Filled Slots	0
Number Of Power Module Free Slots	0
Product Web Sub-Family	Network card pre-installed
Redundant	No

# **Physical**

Height	8.6 cm
Width	48 cm
Depth	68.3 cm
Net Weight	42.22 kg
Mounting Location	Front
Mounting Preference	Lower
Mounting Mode	Rack-mounted
Two Post Mountable	0
Usb Compatible	No

# Input

Input Voltage Limits	151302 V adjustable 160286 V
Network Frequency	50/60 Hz +/- 3 Hz auto-sensing

# Output

Maximum Configurable Power In Va	2200 VA				
Maximum Configurable Power In W	1980 W				
Transfer Time	4 ms typical : 8 ms maximum				
Ups Type	Line interactive				
Wave Type	Sine wave				
Output Frequency	50/60 Hz +/- 3 Hz sync to mains				

## Conformance

Product Certifications	CE EAC IRAM RCM
	VDE  GS Mark

EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018

#### **Environmental**

Acoustic Level	55 dBA
Heat Dissipation	215 Btu/h
Operating Altitude	010000 ft
Ambient Air Temperature For Operation	040 °C
Ambient Air Temperature For Storage	-1545 °C
Storage Altitude	0.0015240.00 m
Relative Humidity	095 %
Storage Relative Humidity	095 %

### **Communications & Management**

Control Panel	Multifunction LCD status and control console					
Emergency Power Off	Optional					
Preinstalled Device	Network management card 3 with environmental monitoring					
Control Panel	LED status display with on line : on battery : replace battery and overload indicators					
Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays					

## **Surge Protection and Filtering**

Surge Energy Rate 375 J

### **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	25.4 cm
Package 1 Width	98 cm
Package 1 Length	60 cm
Package 1 Weight	49.63 kg

### **Contractual warranty**

Warranty 3 years repair or replace (excluding battery) and 2 years for battery



Green Premium<sup>TM</sup> label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO2 products.

Learn more about Green Premium >









Energy Efficient Take-back Transparency RoHS/REACh

R	esc	our	ce	pei	rfor	m	an	ce
• •		<b>-</b>	$\mathbf{c}$	PC.		••••	<b></b>	v

<b>V</b>	nergy Επισιέπτ Product
<b>⊘</b>	ake-Back Program Available

Well-being performance				
<b>⊘</b>	Lead Free			
<b>⊘</b>	Mercury Free			
<b>②</b>	Rohs Exemption Information	Yes		

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information