

# Product datasheet

Specifications



APC Smart-UPS On-Line, 5kVA, Rackmount 3U, 208V/230V, Hard wire 3-wire(2PH+G)+3-wire(H+N+E)+3-wire(H+N+G) outlets, Network Card+SmartSlot, W/ rail kit

SRT5KRMXLW-HW

## Overview

Presentation	High density, double-conversion on-line power protection with scalable runtime.
Lead Time	Usually in Stock


## Main

Main Input Voltage	208 V 230 V
Other Input Voltage	220 V 240 V
Main Output Voltage	208 V 230 V
Other Output Voltage	220 V 240 V
Rated Power In W	4500 W
Rated Power In Va	5000 VA
Output Connector Type	Hard wire 3-wire (H N + E) 1 Hard wire 3-wire (2P + E) 1
Number Of Rack Unit	3U
Provided Equipment	CD with software Documentation CD Installation guide Rack mounting hardware Rack mounting support rails Removable support feet Temperature probe User manual Warranty card Web/SNMP management card

## Batteries & Runtime

Run Time	<a href="#">View Runtime Graph</a>
Efficiency	<a href="#">View Efficiency Graph</a>
Battery Type	Lead-acid battery
Number Of Battery Filled Slots	0
Battery Recharge Time	1.5 h
Number Of Battery Replacement Quantity	1
Battery Voltage	192 V

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Battery Charger Power	560 W rated
Battery Life	3...5 year(s)
Replacement Battery	<a href="#">APCRBC140</a> 
Extended Runtime	1

## General

Ups Type	Double conversion online
Product Web Sub-Family	High density
Number Of Power Module Free Slots	0
Number Of Power Module Filled Slots	0
Redundant	No

## Physical

Colour	Black
Height	13 cm
Width	43.2 cm
Depth	71.9 cm
Net Weight	55.79 kg
Mounting Location	Front
Mounting Preference	Lower
Mounting Mode	Rack-mounted
Two Post Mountable	0
Usb Compatible	Yes
Mounting Position	Horizontal

## Input

Network Frequency	40...70 Hz auto-sensing
Number Of Input Connectors	1 hard wire 3-wire (2P + E) 1 hard wire 3-wire (1P + N + E)
Input Voltage Limits	100...275 V adjustable (half load)

## Output

Maximum Configurable Power In Va	5000 VA
Maximum Configurable Power In W	4500 W
Output Frequency	50/60 Hz +/- 3 Hz sync to mains
Wave Type	Sine wave
Harmonic Distortion	Less than 2 %
Crest Factor	3 : 1
Bypass Type	Internal bypass (automatic and manual)

## Conformance

Product Certifications	CE EAC ENERGY STAR V2.0 (USA) FCC part 15 class A IRAM NOM RCM UL 1778 VDE
Marking	CE Mark
Standards	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018

## Environmental

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 % non-condensing
Operating Altitude	0...10000 ft
Ambient Air Temperature For Storage	-15...45 °C
Storage Relative Humidity	0...95 % non-condensing
Storage Altitude	0.00...15240.00 m
Acoustic Level	55 dBA
Heat Dissipation	931 Btu/h
Ip Degree Of Protection	IP20

## Communications & Management

Free Slots	1
Preinstalled Device	Network management card 3 with environmental monitoring
Alarm	Audible and visible alarms : prioritized by severity
Emergency Power Off	Yes

## Surge Protection and Filtering

Surge Energy Rate	480 J
-------------------	-------

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	33 cm
Package 1 Width	96 cm
Package 1 Length	61 cm
Package 1 Weight	68.04 kg

## Contractual warranty

Warranty	3 years repair or replace (excluding battery) and 2 years for battery
----------	---

Sustainability



**Green Premium™** label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

[Learn more about Green Premium >](#)



Energy Efficient   Take-back   Transparency   RoHS/REACH

Resource performance

- ✓

 Energy Efficient Product
- ✓

 Take-Back Program Available

Well-being performance

- ✓

 Mercury Free
- ✓

 Rohs Exemption Information 

Yes

Environmental Certifications

- ✓

 Energy Star® 

ENERGY STAR UPS V2.0 (USA)

Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	<a href="#">End of Life Information</a>